


Aquaporin Inside® HFFO2 Standard Test Setup

Schematic description of the single-pass testing method used in QC testing of 2.3 m² module



Module specifications

Aquaporin Inside® coating: On lumen side of fiber

Active area (lumen side): 2.3 m²

Inner diameter of fibers: 195 μm

Module dimensions: 300 mm long, 70 mm in diameter

Flow rate of the concentrate was measured on the balance and abstracted from flow rate of the feed in order to calculate water flux through the membrane according to Eq. 1.

$$J_w = \frac{\dot{Q}_{Feed} - \dot{Q}_{Concentrate}}{A} \quad (1)$$

where:

J_w is water flux (L/m²h)
 \dot{Q}_{Feed} is flow rate of feed (L/h)
 $\dot{Q}_{Concentrate}$ is flow rate of concentrate (L/h)
 A is membrane area (m²)

* In order to maintain water flux and reverse salt flux between experiments, it is strongly recommend to flush FO module with DI water after use. We propose to flush the module with DI water for 5 min from the feed and draw side at 25 L/h and subsequently for 30 min only from the feed side at 25 L/h.

Conductivity of the concentrate is measured in order to calculate reverse salt flux according to the Eq. 2.

$$J_s = \frac{\dot{Q}_{Concentrate}}{A} \kappa B \quad (2)$$

where:

J_s is reverse salt flux (g/m²h)
 $\dot{Q}_{Concentrate}$ is flow rate of concentrate (L/h)
 A is membrane area (m²)
 κ is conductivity (μS/cm)
 B is proportionality coefficient (0,5362 μS/cm per 1 mg/L of NaCl)

Aquaporin A/S
 Nymøllevvej 78
 2800 Kongens Lyngby
 Denmark
 Phone: +45 8230 3082
 sales@aquaporin.com
 www.aquaporin.com

Aquaporin Asia Pte Ltd
 1 Cleantech Loop, #02-14
 Cleantech One
 Singapore 637141
 Phone: +65 6268 6343
 sales@aquaporin.asia

Aquapoten Company Ltd.
 12A Shougang International Trade Tower
 No. 60 Xizhimen North Street
 Haidian District, Beijing, 100082, China
 Phone: +86-10-52408461
 business@aquapoten.com
 www.aquapoten.com